

SPEC SHEET

Horizontal Capsule Polisher

HCP- I / II MODELS

INTRODUCTION

Capsule polishers and sorters are machines used in the pharmaceutical industry to clean capsules of their dust.

KEYWORDS polisher | capsule cleaning | surface powder | auxiliary equipment | accessories



TECHNICAL PARAMETERS

Model	HCP- I	HCP- II
Max. Output	300,000 capsules/hour	500,000 capsules/hour
Compressed Air	15m ³ /h 0.3MPa	30m ³ /h 0.3MPa

ATTRIBUTES

- Adjustable angles
- A speed adjustable chamber, cleaning surface powder from capsules
- Polishing chamber with industrial vacuum collector
- Sorting outlet connects to compressed air to collect empty capsules

Motor Power	~220V 50Hz 1A 180w ~110V 60Hz 2A 180w
Dimensions	950×600×1000mm
Net Weight	40kg
Vacuum Cleaning	100m ³ /h -0.014Mpa

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

CONNECT WITH US

+86 577 6688 6278 | info@capsulatech.com | www.captteksolutions.com